

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.598 Wire end ferrules

State: 31/05/2026 (Source: [rittal.com/rs-sr](http://rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.598 - Wire end ferrules on a reel

With plastic collar.

## Features

|                          |   |
|--------------------------|---|
| Model No.                | AS 4051.598   |
| Product description      | With plastic collar.  |
| Technical specifications | Heat-resistant to 105 °C  |
| Material                 | E-Cu, galvanic tin-plated<br>Plastic collar: Polypropylene                      |
| Colour                   | Orange  |
| Length                   | 10 mm   |
| AWG                      | 20  |
| Internal diameter        | 2,6 mm  |
| Rittal colour code       | Yes   |
| For cross-section        | 0,5 mm <sup>2</sup>   |
| Note                     | UL-certified in conjunction with the relevant tools, such as crimping machines. |
| Standards                | AEH DIN 46228   |
| Delivery form            | Taped   |
| Packs of                 | 5.000 pc(s).  |
| Net weight               | 5 kg  |
| Gross weight             | 0,589 kg  |
| Customs tariff number    | 85369010  |
| ETIM 9                   | EC000005  |
| ETIM 8                   | EC000005  |
| ECLASS 8.0               | 36659290  |

# Features

---

Product description

Wire end ferrules 0.5 mm<sup>2</sup> x 10 mm AWG 20, packs of 5,000 pc(s)., colour: orange, delivery form: on belt (in accordance with the Rittal colour code)

# Approvals

---

Approvals

UL + C-UL (listed)