

Rittal – The System.

Faster – better – everywhere.



AS 4051.599 Wire end ferrules

State: 08/07/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.599 - Wire end ferrules on a reel

With plastic collar.

Features

Model No.	AS 4051.599
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	White
Length	8 mm
AWG	18
Internal diameter	2,8 mm
Rittal colour code	Yes
For cross-section	0,75 mm ²
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	5.000 pc(s).
Net weight	5 kg
Gross weight	0,598 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end ferrules for crimping machines, 0.75 mm ² , AWG 18, 8 mm, orange, on belt, 5000 pc(s).

Approvals

Approvals

UL + C-UL (listed)

UR