

Rittal – The System.

Faster – better – everywhere.



AS 4055.180

Splitter hole punch set, metric

State: 23/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.180 - Splitter hole punch set, metric for stainless steel, round, with triple splitting

For punching round cut-outs

Features

Model No.	AS 4055.180
Design	With triple splitting
Product description	For punching round cut-outs. The hole punch is operated with a wrench or hydraulic punch.
Supply includes	5 female dies 5 male dies Plastic case
Machinable material	Stainless steel
For threads	M16 M20 M25 M32 M40
Note	When operating with wrenches, tension screws with ball bearings should be used.
Max. machinable material thickness, stainless steel / diameter of hole punch / to fit hydraulic screw Model No. / to fit tension screw Model No.	2 mm / 16.2 mm / 4,055,665 / 4,055.632 2 mm / 20.4 mm / 4,055,665 / 4,055.632 2 mm / 25.4 mm / 4,055,665 / 4,055.632 2.5 mm / 32.5 mm / 4,055,663 / 4,055.633 2.5 mm / 40.5 mm / 4,055,663 / 4,055.634
Packs of	1 pc(s).
Net weight	0,849 kg
Gross weight	1,098 kg
Customs tariff number	82073010
ETIM 9	EC002121

Features

ETIM 8	EC002121
ECLASS 8.0	21049047
Product description	Splitter hole punch set, metric for stainless steel, round, with triple splitting
