

Rittal – The System.

Faster – better – everywhere.



TS 4695.000 Support strip

State: 21/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 4695.000 - Support strip for VX, TS, VX SE, TP, AX

For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.



Features

Model No.	TS 4695.000
Product description	For simple attachment of cable ducts, cable conduit holders, contact hazard protection cover plates, equipment installed on the door, cable clamping and attachment.
Technical specifications	4.5 mm diameter hole on a 25 mm pitch pattern
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Length	440 mm
VX installation options	In enclosure depth 500 mm
VX SE installation options	In enclosure depth 500 mm, on the outer mounting level
AX installation options	In door width 500 mm, with cam lock In door width 500 mm, with 3-point lock system, in the hinged door
AX stainless steel installation options	In door width 500 mm, in hinged door, in conjunction with the perforated door strip
TS installation options	In enclosure width/depth 500 mm, on the outer mounting level
AE installation options	In enclosure width/height 500 mm, in conjunction with rail for interior installation AE

Features

TP installation options	In TP pedestal and one-piece console pedestal, in enclosure depth 500 mm, in conjunction with rail for interior installation for TP, compact enclosure HD
To fit	Enclosure type: VX TS VX SE TP AX AE Width/depth: 500 mm
Packs of	20 pc(s).
Net weight	4,4 kg
Gross weight	4,603 kg
PCF per pack (cradle-to-gate)	21 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261
Product description	TS Support strip, for VX, TS, VX SE, TP, for outer mounting level: for W/D: 500 mm, L: 440 mm

Approvals

Explanations	PCF-declaration
--------------	-----------------