

Rittal – The System.

Faster – better – everywhere.



DK 5502.115 Cable finger

State: 21/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5502.115 - Cable finger for VX IT

For U-based cable routing.

Features

Model No.	DK 5502.115
Design	for VX IT 482.6 mm (19") mounting angles, standard
Product description	For structured cable routing on the 482.6 mm (19") mounting level in 1 U increments.
Benefits	Simple, tool-free installation by snap-mounting directly into the 482.6 mm (19") mounting angle
Material	Plastic to UL 94-V0
Colour	RAL 9005
Installation options	Installation is possible both on the front and on the side of the mounting angles at the front and rear
Note	Cable routing in conjunction with air baffle plates is supported
Dimensions	Width: 14 mm Length: 261 mm
Units	6 U
Packs of	14 pc(s).
Net weight	0,784 kg
Gross weight	0,937 kg
Customs tariff number	39269097
ETIM 9	EC000322
ECLASS 8.0	27400703
Product description	DK Cable finger for TS-IT, 6 U, RAL 9005