

Rittal – The System.

Faster – better – everywhere.



DK 7113.000 Earth rail, horizontal

State: 14/04/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7113.000 - Earth rail, horizontal

Potential equalisation rail, current carrying capacity approx. 200 A.

Features

Model No.	DK 7113.000
Product description	Current carrying capacity approx. 200 A.
Supply includes	Earth rail made from E-Cu 57 to DIN EN 12 163, DIN EN 13 601, 15 x 5 mm 20 connection points with M5 screws 2 earth connections 25 mm ² 2 isolators Assembly parts
Dimensions	Width: 15 mm Height: 5 mm Length: 450 mm
To fit	Enclosure type: AX VX VX IT TS TS IT AX wall-mounted enclosure, 3-part Width: > 600 mm Depth: > 600 mm Width/depth: 800 mm
Packs of	1 pc(s).
Net weight	0,402 kg
Gross weight	0,436 kg
Customs tariff number	74198090
ETIM 9	EC000329
ECLASS 8.0	27400605
Product description	DK earth rail, horizontal, length 450 mm, W/D: >600 mm

Approvals

Explanations

Manufacturer's declaration

Tender text

Earth rail / potential equalisation rail

For installing in network and server enclosures or wall-mounted distribution enclosures, W/D: >600 mm. The E-Cu 57 earth rail has two isolators, 20 M5 earth connections and two 25 mm earth connections. The rail's current carrying capacity is 200A.

Earthing rail length: 450 mm