

Rittal – The System.

Faster – better – everywhere.



DK 7396.000 Data Rack

State: 07/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7396.000 - Data Rack

Data Rack for optimum accessibility from all sides during assembly and installation as well as extensive mobility when using twin castors.



Features

| | |
|--|---|
| Model No. | DK 7396.000 |
| Material | Profile frame, base/plinth: Sheet steel Feet: Die-cast zinc |
| General colour | RAL 7035 |
| Colour | Profile frame, base/plinth: RAL 7035 Trim panel, feet: RAL 5018 |
| Supply includes | Torsionally stiff profile frame with 482.6 mm (19") punchings Stable base/plinth with integral feet, with the option of floor anchoring without base trim panels Mounting accessories |
| Dimensions | Width: 550 mm Height: 1,722 mm Depth: 750 mm |
| Units | 36 U |
| Units | 36 U |
| Distance from the second mounting level, 50 mm pitch pattern | 150 - 350 mm |

Features

| | |
|---|--|
| Pitch pattern between the mounting levels | 50 mm |
| Load capacity of the 482.6 mm (19") mounting angles | 1.500 N |
| Note | Order second mounting level separately |
| Basic material | Sheet steel |
| Packs of | 1 pc(s). |
| Net weight | 15,1 kg |
| Gross weight | 18,5 kg |
| PCF per pack (cradle-to-gate) | 71.1 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94032080 |
| ETIM 9 | EC002507 |
| ECLASS 8.0 | 27180602 |
| Product description | DK Data Rack distributor rack, WHD: 550x1721,8x750 mm, 36 U, RAL 7035 |

Tender text

482.6 mm (19 inch) rack, 36 U

Torsionally stiff frame section, welded from 2 mm sheet steel, with integral 482.6 mm (19 inch) punchings and round and square holes in the 25 mm DIN pitch pattern for accommodation of cabling systems and 482.6 mm (19 inch) components.

The rack is depth-adjustable in a pitch pattern of 50 mm on a folded sheet steel base/plinth with die-cast zinc feet. The base/plinth can accommodate a second 482.6 mm (19 inch) mounting level, offers the option of floor anchoring and fastening facilities for levelling feet and castors.

Infinitely bayable.

Material: Sheet steel

Colour: RAL 7035

Dimensions: Rack height 1722 mm, 36 U,

base/plinth: WxD: 550 x 750 mm