

Rittal – The System.

Faster – better – everywhere.



DK 7492.500 Slide rail, heavy-duty

State: 21/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7492.500 - Slide rail, heavy-duty for TS network enclosures with two mounting levels

For TS network enclosures with two 482.6 mm (19") mounting levels, to support heavy installed equipment.

Features

Model No.	DK 7492.500
Design	For static installation between two 482.6 mm (19") mounting levels.
Product description	To support heavy installed equipment. The slide rails are simply located into the cranked mounting angles and secured with screws. The combined use with additional depth stays or, in case of 80 mm wide enclosures, with the additional fastening attachment counteracts possible bending of the mounting angles in case of unevenly distributed loads.
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Distance between mounting levels	498 mm
Load capacity	80 kg, static load
Note	Not suitable in combination with 482.6 mm (19") mounting frame Please select slide rails according to the relevant 482.6 mm (19") distance between levels. If combining with L-shaped mounting angles, a mounting adaptor for L-shaped mounting angles must be used.
Contact surface	Width: 55 mm Depth: 461 mm
Packs of	2 pc(s).
Net weight	1 kg
Gross weight	1,24 kg
Customs tariff number	73269098

Features

ETIM 9	EC002620
ECLASS 8.0	27189261

Tender text

Heavy-duty slide rail

For attaching to L-shaped TS mounting angle adaptor DK
7827.300

Material: Sheet steel, zinc-plated, passivated

Dimensions (W x H x D): 0 mm x 0 mm x 461 mm