


Rittal – The System.

Faster – better – everywhere.



DK 7825.380

Gland plate modules, vented

State: 21/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7825.380 - Gland plate modules, vented for TS IT, TS, SE, TX CableNet

Gland plate modules, vented, for TS, TS IT, SE for use in the base frame of the network enclosure. Used in exchange for an existing gland plate of the same depth.

Features

| | |
|-------------------------------|--|
| Model No. | DK 7825.380 |
| Product description | Large perforated section for passive enclosure ventilation. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Filter mat and nylon tape |
| Note | Several gland module plates need to be combined to close off the base completely in the TS-IT |
| Dimensions | Depth: 237.5 mm |
| To fit | Enclosure type: TS TS IT SE TX CableNet Width: 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 1,95 kg |
| Gross weight | 2,26 kg |
| PCF per pack (cradle-to-gate) | 8.2 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Features

Product description

DK Gland plate module, vented, depth: 237,5 mm, for enclosure width: 800 mm, for TS, TS IT, SE, TX CableNet, sheet steel, zinc-plated

Tender text

Gland plate module, vented

For W: 800 mm,

Depth: 237,5 mm

For TS, TS IT, SE, TX CableNet

For cable entry with brush

Sheet steel, vented