

Rittal – The System.

Faster – better – everywhere.



SZ 7967.000

Spacer

State: 22/05/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 7967.000 - Spacer for roof plate

To raise the roof for ventilation purposes, in three different heights. Not suitable for crane transportation.



Features

Model No.	SZ 7967.000
Product description	To raise the roof for ventilation purposes, in three different heights.
Material	Hexagon steel section
Surface finish	Zinc-plated
Supply includes	Assembly parts
Assembly instruction	Not suitable for combination with 482.6 mm (19") mounting frame Not suitable for crane transportation
Dimensions	Height: 50 mm
Dimensions	Thread: M12
To fit	Enclosure type: VX TS
Packs of	4 pc(s).
Net weight	0,444 kg
Gross weight	0,539 kg
PCF per pack (cradle-to-gate)	2.1 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098

Features

ETIM 9	EC002625
ECLASS 8.0	27189234
Product description	DK Spacer, L: 50 mm, For TS roof plate

Tender text

Spacers, 50 mm

Material: Hexagonal sectional steel, zinc-plated,
passivated,