

# Rittal – The System.

Faster – better – everywhere.



## TS 8602.050

## Base/plinth trim panels, side, 200 mm

State: 23/07/2026 (Source: [rittal.com/rs-sr](https://www.rittal.com/rs-sr))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# TS 8602.050 - Base/plinth trim panels, side, 200 mm for base/plinth components front and rear

For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used.

## Features

|                       |                                                                                                                                                                                    |
|-----------------------|------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No.             | TS 8602.050                                                                                                                                                                        |
| Product description   | For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used.                                                                       |
| Material              | Sheet steel                                                                                                                                                                        |
| Surface finish        | Spray-finished                                                                                                                                                                     |
| Colour                | RAL 7022                                                                                                                                                                           |
| Supply includes       | 2 base/plinth trim panels<br>Assembly parts                                                                                                                                        |
| Assembly instruction  | Base/plinth trim panels, side, 100 mm, may be installed rotated through 90° to stabilise bayed base/plinth components. The base/plinth baying bracket is required for this purpose |
| Dimensions            | Height: 200 mm                                                                                                                                                                     |
| To fit                | Enclosure type: TS: = 500 mm<br>Enclosure type: SE<br>Enclosure type: CM<br>Enclosure type: TP<br>Enclosure type: PC<br>Enclosure type: IW<br>Enclosure type: TS IT                |
| Packs of              | 2 pc(s).                                                                                                                                                                           |
| Net weight            | 2,7 kg                                                                                                                                                                             |
| Gross weight          | 2,716 kg                                                                                                                                                                           |
| Customs tariff number | 94039910                                                                                                                                                                           |
| ECLASS 8.0            | 27182003                                                                                                                                                                           |

# Features

---

|                     |                                                                       |
|---------------------|-----------------------------------------------------------------------|
| Product description | TS Trim panel, sides, H: 200 mm, for W: 500 mm, RAL 7022, sheet steel |
|---------------------|-----------------------------------------------------------------------|