



VX 8700.050 - Side panels, screw-fastened, stainless steel for VX

Side panels, screw-fastened, stainless steel, for VX.

Features

Model No.	VX 8700.050
Benefits	Time-saving assembly thanks to clip-in side panel holder Automatic potential equalisation and higher EMC protection, thanks to enclosure panel holders with earthing inserts located on the inside Easy positioning in the height and depth with the location aid One-person assembly Earthing bolts with large, paint-free contact surface for optimum contact
Material	Stainless steel 1.4301 (AISI 304), 1.5 mm
Surface finish	Brushed, grain 400
Supply includes	Assembly parts
To fit	Enclosure type: VX Height: = 2,000 mm Depth: = 600 mm
IP protection category to IEC 60529	IP 55 IP 66
Type rating to UL 50E	Type 1 Type 3R Type 4 Type 4X Type 12
Basic material	Stainless steel
Packs of	2 pc(s).
Net weight	27,8 kg
Gross weight	28,8 kg

Features

Customs tariff number	94039910
ETIM 9	EC002524
ECLASS 8.0	27182101
Product description	VX Side panel, screw-fastened, for HD: 2000x600 mm, stainless steel, 1.4301

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------