

Rittal – The System.

Faster – better – everywhere.



SV 9635.340 Component adaptor

State: 07/06/2026 (Source: rittal.com/rs-sr)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.340 - Component adaptor 3-pole

For assembly of switchgear and protective gear.

Features

| | |
|------------------------------|--|
| Model No. | SV 9635.340 |
| Design | Comfort |
| Function principle | For mechanical attachment and direct contacting of electrical equipment on the board |
| Material | Polyamide Fire protection corresponding to UL 94 |
| Colour | RAL 7035 |
| Note | The technical data may vary for UL applications |
| Rated current max. | 25 A |
| Rated operating voltage | 600 V (DC), 3~ 690 V (AC), 3~ |
| Number of poles | 3-pole |
| Electrical ratings UL | Rated operating voltage (max.) UL: 600 V AC |
| Connection cables (AWG) | AWG 12 |
| Length of connection cable | 100 mm |
| Support rails Qty/height | 1 / 10 mm |
| Support rail type | adjustable |
| Dimensions | Width: 45 mm Height: 160 mm Depth: 34.5 mm |
| Packs of | 4 pc(s). |
| Net weight | 0,512 kg |
| Gross weight | 0,518 kg |
| Copper weight (kg per piece) | 0,03 |

Features

| | |
|-----------------------|--|
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Component adaptor (Comfort), 25 A, 690 V (AC), 600 V (DC), 3-pole, connection cable AWG 12 (L: 100 mm), WH: 45x160 mm |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |
