

# Rittal – The System.

Faster – better – everywhere.



## KX 1552.000

## E-box KX, stålplåt

State: 2025-06-01 (Source: [rittal.com/se-sv](http://rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KX 1552.000 - E-box KX, stålplåt

Kopplingslådan KX, E-Box KX, i stålplåt ger hög montagekomfort samt flexibilitet vid val av låssystem.



## Features

Art. nr.	KX 1552.000
Produktbeskrivning	Kopplingslådan KX, E-Box KX, i stålplåt ger hög montagekomfort samt flexibilitet vid val av låssystem.
Material	Skåp: Stålplåt Dörr: Stålplåt, omgivande inskummad PU-tätning
Ytbehandling	Skåp och dörr: Doppgrunderade, pulverlackerade på utsidan, strukturlack Montageplåt: förzinkad
Färg	RAL 7035
Leveransens omfattning	Skåp med dörr Montageplåt Vridlås med 3 mm låsinsats 180°-gångjärn
Protection category NEMA	NEMA 1 NEMA 3R NEMA 4 NEMA 12
Kapslingsklass IP enligt EN 60 529	IP 66

# Features

Typklassning motsvarande UL 50E	Typ 1 Type 3R Type 4 Typ 12
IK-kod	IK08
Dimension	Bredd: 200 mm Höjd: 300 mm Djup: 80 mm
Mått för montageplåt (B × H)	175 mm x 285 mm
Materialtjocklek låda	1,25 mm
Materialtjocklek dörr	1,25 mm
Materialtjocklek montageplåt	2 mm
Lås	Antal lås: 1
Grundmaterial	Stålplåt
Förpackningsenhet	1 st.
Nettovikt	2.923
Bruttovikt	3.18
PCF per pack (cradle-to-gate)	11 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Tullvarukod	94032080
EAN	4028177816541
E-Number Sweden	E3465220
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101

# Approvals

---

## Approvals

Bureau Veritas  
DNV-GL  
Lloyds Register of Shipping  
UL + C-UL (listed)

---

## Certificates

Kapslingsklass

---

## Explanations

Tillverkarens deklARATION  
Konformitetsförklaring  
Konformitetsförklaring UK  
PCF-declaration