


# Rittal – The System.

Faster – better – everywhere.



## BG 1558.010 Bus-skåp BG

State: 2026-05-09 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# BG 1558.010 - Bus-skåp BG Rostfritt stål

Bus-skåp av rostfritt stål 1.4301, (AISI 304), inkl. 180°-gångjärn. Kapslingsklass IP 66.

## Features

Art. nr.	BG 1558.010
Material	Skåp: Rostfritt stål 1,4301 (AISI 304) Lock: Rostfritt stål 1.4301 (AISI 304), omgivande inskummad PU-tätning 180°-gångjärn: zinkjutgods
Ytbehandling	Skåp och lock: Streckslipat, korn 240 180°-gångjärn: kromade
Leveransens omfattning	Skåp med lock 180°-gångjärn (2 stycken) Profilskena TH 35/7,5 Snabbkoppling inkl. plasthylsor
Protection category NEMA	NEMA 4X
Kapslingsklass IP enligt EN 60 529	IP 66
Dimension	Bredd: 400 mm Höjd: 200 mm Djup: 123 mm
Materialtjocklek låda	1,5 mm
Materialtjocklek dörr	1,25 mm
Position dörrupphängning	nedtill
Antal profilskenor	1
Lås	Utförande för lås: Snabbkoppling inkl. plasthylsor Antal lås: 2
Grundmaterial	Rostfritt stål 1.4301 (AISI 304)
Förpackningsenhet	1 st.
Nettovikt	3,92 kg
Bruttovikt	4,12 kg

# Features

---

Tullvarukod	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Produktbeskrivning	BG Busskåp, BHD: 400 x 200 x 123 mm, rostfritt stål 1.4301, utan montageplåt, med lock, profilskena

# Approvals

---

Approvals	Lloyds Register UL + C-UL (listed)
Explanations	Konformitetsförklaring Konformitetsförklaring UK