

Rittal – The System.

Faster – better – everywhere.



SM 2384.040

Tryckknappslåda

State: 2026-06-27 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SM 2384.040 - Tryckknappslåda Rostfritt stål

Tryckknappslåda av rostfritt stål 1.4301, (AISI 304), med knapputskränningar Ø 22,5 mm.
Kapslingsklass IP 66.

Features

Art. nr.	SM 2384.040
Material	Skåp: Rostfritt stål 1,4301 (AISI 304) Lock: Rostfritt stål 1.4301 (AISI 304), omgivande inskummad PU-tätning
Ytbehandling	Skåp och lock: Streckslipat, korn 240
Leveransens omfattning	Skåp med lock Snabbkoppling inkl. plasthylsor
Protection category NEMA	NEMA 4X
Kapslingsklass IP enligt EN 60 529	IP 66
IK-kod	IK08
Dimension	Bredd: 280 mm Höjd: 100 mm Djup: 90 mm
Materialtjocklek lock	1,25 mm
Materialtjocklek låda	1,25 mm
Rastermått	60 mm
Öppningar (antal x Ø)	4 x 22,5 mm
Lås	Utförande för lås: Snabbkoppling inkl. plasthylsor Antal lås: 4
Kabelinföring (antal x Ø)	4
Antal metrisk förpräglingar	4
Grundmaterial	Rostfritt stål 1.4301 (AISI 304)
Förpackningsenhet	1 st.
Nettovikt	1,4 kg

Features

Bruttovikt	1,501 kg
PCF per paket (Cradle-to-Gate)	5,1
Tullvarukod	84879090
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Produktbeskrivning	SM Tryckknappslåda, BHD: 280x100x90 mm rostfritt stål 1.4301, utan montageplåt, 4 knappskärningar

Approvals

Explanations	Konformitetsförklaring Konformitetsförklaring UK PCF-declaration
--------------	--