

Rittal – The System.

Faster – better – everywhere.



AS 4051.536

Ändhylsor

State: 2026-03-12 (Source: rittal.com/se-sv)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.536 - Ändhylsor på rulle

Med plastkragar.

Features

Art. nr.	AS 4051.536
Produktbeskrivning	Med plastkragar.
Tekniska data	Värmetålig upp till 105 °C
Material	E-Cu, galvaniskt förzinkad Plastkrage: Polypropylen
Färg	orange
Längd	10 mm
AWG	20
Inre diameter	2,9 mm
Rittal-färgkod	Yes
För tvärsnitt	0,5 mm ²
Multinorm	Yes
Observera:	UL-certifierad i kombination med motsvarande verktyg, som t.ex. crimpmaskin.
Levererat utförande	på bälte
Förpackningsenhet	4 000 st.
Tullvarukod	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Produktbeskrivning	Wire end ferrules 0.5 mm ² x 10 mm AWG 20 multinorm, packs of 4,000 pc(s)., colour: orange, delivery form: on belt (in accordance with the Rittal colour code), 0.5 mm ²

Approvals

Approvals

UL + C-UL (listed)