

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.544

## Ändhylsor

State: 2026-06-02 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.544 - Ändhylsor på rulle

Med plastkragar.

## Features

|                     |  |
|---------------------|--|
| Art. nr.            | AS 4051.544  |
| Produktbeskrivning  | Med plastkragar.   |
| Tekniska data       | Värmetålig upp till 105 °C   |
| Material            | E-Cu, galvaniskt förzinkad<br>Plastkrage: Polypropylen   |
| Färg                | vit  |
| Längd               | 10 mm  |
| AWG                 | 20   |
| Inre diameter       | 2,9 mm   |
| För tvärsnitt       | 0,5 mm <sup>2</sup>  |
| DIN-färgkod         | Yes  |
| Multinorm           | Yes  |
| Observera:          | UL-certifierad i kombination med motsvarande verktyg, som t.ex. crimpmaskin.   |
| Levererat utförande | på bälte   |
| Förpackningsenhet   | 4 000 st.  |
| Nettovikt           | 4 kg   |
| Tullvarukod         | 85369010   |
| ETIM 9              | EC000005   |
| ETIM 8              | EC000005   |
| ECLASS 8.0          | 36659290   |
| Produktbeskrivning  | Wire end ferrules 0.5 mm <sup>2</sup> x 10 mm AWG 20 multinorm, packs of 4,000 pc(s)., colour: white, delivery form: on belt (in accordance with the DIN colour code), 0.5 mm <sup>2</sup> |

# Approvals

---

Approvals

UL + C-UL (listed)