

Rittal – The System.

Faster – better – everywhere.



AS 4051.597

Ändhylsor

State: 2026-03-27 (Source: rittal.com/se-sv)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.597 - Ändhylsor på rulle

Med plastkragar.

Features

Art. nr.	AS 4051.597
Produktbeskrivning	Med plastkragar.
Tekniska data	Värmetålig upp till 105 °C
Material	E-Cu, galvaniskt förzinkad Plastkrage: Polypropylen
Färg	orange
Längd	8 mm
AWG	20
Inre diameter	2,6 mm
Rittal-färgkod	Yes
För tvärsnitt	0,5 mm ²
Observera:	UL-certifierad i kombination med motsvarande verktyg, som t.ex. crimpmaskin.
Standarder	AEH DIN 46228
Levererat utförande	på bälte
Förpackningsenhet	5 000 st.
Nettovikt	5 kg
Bruttovikt	0,536 kg
Tullvarukod	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290

Features

Produktbeskrivning

Wire end ferrules for crimping machines, 0.5 mm², AWG 20, 8 mm, orange, on belt, 5000 pc(s).

Approvals

Approvals

UL + C-UL (listed)
UR