

Rittal – The System.

Faster – better – everywhere.



AS 4051.598

Ändhylsor

State: 2026-05-31 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.598 - Ändhylsor på rulle

Med plastkragar.

Features

| | |
|---------------------|--|
| Art. nr. | AS 4051.598 |
| Produktbeskrivning | Med plastkragar. |
| Tekniska data | Värmetålig upp till 105 °C |
| Material | E-Cu, galvaniskt förzinkad Plastkrage: Polypropylen |
| Färg | orange |
| Längd | 10 mm |
| AWG | 20 |
| Inre diameter | 2,6 mm |
| Rittal-färgkod | Yes |
| För tvärsnitt | 0,5 mm ² |
| Observera: | UL-certifierad i kombination med motsvarande verktyg, som t.ex. crimpmaskin. |
| Standarder | AEH DIN 46228 |
| Levererat utförande | på bälte |
| Förpackningsenhet | 5 000 st. |
| Nettovikt | 5 kg |
| Bruttovikt | 0,589 kg |
| Tullvarukod | 85369010 |
| ETIM 9 | EC000005 |
| ETIM 8 | EC000005 |
| ECLASS 8.0 | 36659290 |

Features

| | |
|--------------------|---|
| Produktbeskrivning | Wire end ferrules 0.5 mm ² x 10 mm AWG 20, packs of 5,000 pc(s)., colour: orange, delivery form: on belt (in accordance with the Rittal colour code) |
|--------------------|---|

Approvals

| | |
|-----------|--------------------|
| Approvals | UL + C-UL (listed) |
|-----------|--------------------|