


Rittal – The System.

Faster – better – everywhere.



AS 4051.605 Ändhylsor

State: 2026-04-19 (Source: rittal.com/se-sv)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.605 - Ändhylsor på rulle

Med plastkragar.

Features

Art. nr.	AS 4051.605
Produktbeskrivning	Med plastkragar.
Tekniska data	Värmetålig upp till 105 °C
Material	E-Cu, galvaniskt förzinkad Plastkrage: Polypropylen
Färg	blå
Längd	10 mm
AWG	14
Inre diameter	4,2 mm
För tvärsnitt	2,5 mm ²
DIN-färgkod	Yes
Observera:	UL-certifierad i kombination med motsvarande verktyg, som t.ex. crimpmaskin.
Standarder	AEH DIN 46228
Levererat utförande	på bälte
Förpackningsenhet	3 000 st.
Nettovikt	3 kg
Tullvarukod	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Produktbeskrivning	Wire end ferrules 2.5 mm ² x 10 mm AWG 14, packs of 3,000 pc(s)., colour: blue, delivery form: on belt (in accordance with the DIN/Rittal colour code)

Approvals

Approvals

UL + C-UL (listed)