


Rittal – The System.

Faster – better – everywhere.



AS 4051.730

Ändhylsor

State: 2026-03-14 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4051.730 - Ändhylsor lös

Med plastkragar.

Features

Art. nr.	AS 4051.730
Produktbeskrivning	Med plastkragar.
Tekniska data	Värmetålig upp till 105 °C
Material	E-Cu, galvaniskt förzinkad Plastkrage: Polypropylen
Färg	orange
Längd	18 mm
AWG	12
Inre diameter	4,8 mm
DIN-färgkod	Yes
Observera:	UL-certifierad i kombination med motsvarande verktyg, som t.ex. crimpmaskin. Kontakta din Rittal-rådgivare för enskild konsultation.
Standarder	AEH DIN 46228
Levererat utförande	lös
Förpackningsenhet	100 st.
Nettovikt	0,1
Tullvarukod	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Produktbeskrivning	Ändhylsor för kabelmontering, 4,0 mm ² , orange, lösa, 18 mm

Approvals

Approvals

UL + C-UL (listed)

UR