

Rittal – The System.

Faster – better – everywhere.



AS 4055.070

**Manuell hydraulstanssats M16–
M63**

State: 2026-07-09 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4055.070 - Manuell hydraulstanssats M16–M63

Manuell hydraulstans i praktisk sats med plåtstans för stålplåt. Maximal bearbetningsbar materialtjocklek 2 eller 3 mm.

Features

Art. nr.	AS 4055.070
Utförande	Denna sats innehåller standardplåtstans M16 till M63.
Produktbeskrivning	Manuell hydraulstans i praktisk set med stansar för stålplåt. Maximal bearbetningsbar materialtjocklek 2 eller 3 mm.
Fördelar	Förlängd hållbarhet för verktyg tack vare inbyggd övertrycksventil
Leveransens omfattning	Manuell hydraulstans, rak 7 distanser med 3-delad splitterfunktion Hydraulskruv Ø 19 mm Hydraulskruv Ø 9,5/19 mm HSS borrar Ø 10 mm Distanshylssats (3-delad) Plastfodral
Material som kan bearbetas	Stålplåt
Max. bearbetningsbar materialtjocklek för stålplåt	2 mm 2 mm 2 mm 3 mm 3 mm 3 mm 3 mm
Ø-stans	16,2 mm 20,4 mm 25,4 mm 32,5 mm 40,5 mm 50,5 mm 63,5 mm

Features

För gänga	M16 M20 M25 M32 M40 M50 M63
Förpackningsenhet	1 st.
Nettovikt	5,3 kg
Bruttovikt	5,34 kg
Tullvarukod	82034000
ETIM 9	EC002121
ETIM 8	EC002121
ECLASS 8.0	21049046
Produktbeskrivning	Hand hydraulic punch set straight M16,20,25,32,40,50,63 mm
