



Rittal – The System.

Faster – better – everywhere.



RX 9360.513

RiLineX Circuit-breaker component adaptor

State: 2025-08-02 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.513 - RiLineX Circuit-breaker component adaptor

CB component adaptors for the RiLineX busbar platform in widths 81 to 140 mm. For mounting moulded-case circuit-breakers (MCCBs). Products are available in two variants: An "Easy-Fix" variant for user-friendly external mounting of switches from all standard manufacturers, and a "Universal" variant with U nuts for maximum flexibility.

Features

Art. nr.	RX 9360.513
Utförande	Easy Fix
Fördelar	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamid (PA 6) Brandklassad enligt UL 94
Färg	RAL 9005 RAL 35745
Kapslingsklass IP enligt IEC 60 529	IP 2XB
Märkström max.	250 A
Märkström (UL)	210 A
Märkstötspänning Uimp	12 kV
Rated voltage	690 V AC 690 V DC 600 V AC (UL)
Rated insulation voltage	1 000 V
Överspänningskategori	4
Nedsmutsningsgrad	3
Poltal	3-polig

Features

Kabelutgång	uppe
Anslutningstyp (elektrisk)	Skruv M8
Passar för samlingsskenesystemet	RiLineX RiLine60
Frekvens för grundtonssvängning	50...60 Hz
Luftfuktighet (ej kondenserande)	10...90 %
Passar för samlingsskenor	15 × 5/10 20 x 5/10 30 x 5/10
Drifttemperatur	-25 °C...55 °C
Förvaringstemperatur	-25 °C...75 °C
Dimension	Bredd: 105 mm Höjd: 252 mm Djup: 63 mm
Förpackningsenhet	1 st.

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------