


Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX anslutningsadapter

State: 2026-05-21 (Source: rittal.com/se-sv)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.300 - RiLineX anslutningsadapter

RiLineX connection adaptor for 60 mm busbar systems. The connection adaptor is single-pole and only suitable for flat copper bars. The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adaptor boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The terminals support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adaptor is readily installed on RiLine60. It offers high levels of short-circuit protection and easy-to-fit contact hazard protection.



Features

Art. nr.	RX 9361.300
Fördelar	Montage i samlings-skensystem och kabelanslutning med bara en skruv
Material	Polyamid (PA 6) Brandklassad enligt UL 94
Färg	RAL 9005
Märkström (max.)	1 500 A
Märkström max.	1 500 A
Mätström laminerad kopparskena	1 500 A
Mätström laminerad kopparskena (UL)	1 380 A

Features

Elektriska värden UL(SCCR)	52,5 kA - 600 V, RMS, unprotected 100 kA – 480 V, effektbrytare max 800 A, DIVQ/7 100 kA – 600 V, säkring klass L max 2000 A, JDDZ/7
Kabelutgång	uppe/nedtill
För skensystem med centrumavstånd	60 mm
Poltal	1-polig
Passar för samlingsskenesystemet	RiLineX RiLine60
Dimension	Bredd: 72,3 mm Höjd: 119,4 mm Djup: 117,4 mm
Klämutrymme för laminerade kopparskenor (B x H)	50 x 20 mm
Passar för samlingsskenor	15 × 10 20 × 10 30 × 10
Märkspänning	1 000 V AC 1 500 V DC 600 V AC (UL) 600 V DC (UL)
Överspänningskategori	4
Nedsmutningsgrad	3
Standarder	IEC/EN 61439-1 UL 508
Märkstötspänning Uimp	12 kV
Märkisolationsspänning Ui	1 000 V
Kapslingsklass IP enligt IEC 60 529	IP 2XB
Luftfuktighet i driftsmiljö max.	90 %
Driftstemperatur	-5 °C...55 °C
Förvaringstemperatur	-25 °C...75 °C

Features

Luftfuktighet (ej kondenserande)	10...90 %
Antal anslutningar	2
Förpackningsenhet	1 st.
Nettovikt	0,65 kg
Bruttovikt	0,688 kg
PCF per paket (Cradle-to-Gate)	2,69
Tullvarukod	85369010
ETIM 9	EC001531
Produktbeskrivning	RiLineX connection adaptor for 60 mm busbar systems. The connection adaptor is single-pole and only suitable for flat copper bars. The phase spacing is freely selectable. The unit is suitable for use with L1/L2/L3/N. The adaptor boasts an impressive compact design. Dismantling requires the use of tools. Conductors may be connected either from above or below. The connection clamps support full through-wiring. Mounted by simply snapping onto the RiLineX board. The adaptor is readily installed on RiLine60. It boasts high levels of short-circuit protection and easy-to-fit contact hazard protection.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Konformitetsförklaring PCF-declaration