


Rittal – The System.

Faster – better – everywhere.



RX 9361.300

RiLineX anslutningsadapter

State: 2026-04-06 (Source: rittal.com/se-sv)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9361.300 - RiLineX anslutningsadapter

RiLineX connection adaptor for 60 mm busbar systems. To fit double connection (bar). Freely selectable phase difference. Only suitable for 10 mm busbars.



Features

Art. nr.	RX 9361.300
Fördelar	Montage i samlingsskenssystem och kabelanslutning med bara en skruv
Material	Polyamid (PA 6) Brandklassad enligt UL 94
Färg	RAL 9005
Märkström (max.)	1 500 A
Märkström max.	1 500 A
Mätström laminerad kopparskena	1 500 A
Mätström laminerad kopparskena (UL)	1 380 A
Elektriska värden UL(SCCR)	52,5 kA - 600 V, RMS, unprotected 100 kA – 480 V, effektbrytare max 800 A, DIVQ/7 100 kA – 600 V, säkring klass L max 2000 A, JDDZ/7
Kabelutgång	uppe/nedtill
För skensystem med centrumavstånd	60 mm

Features

Poltal	1-polig
Passar för samlingskenesystemet	RiLineX RiLine60
Dimension	Bredd: 72,3 mm Höjd: 119,4 mm Djup: 117,4 mm
Klämutrymme för laminerade kopparskenor (B x H)	50 x 20 mm
Passar för samlingskenor	15 × 10 20 × 10 30 × 10
Märkspänning	1 000 V AC 1 500 V DC 600 V AC (UL) 600 V DC (UL)
Överspänningskategori	4
Nedsmutningsgrad	3
Standarder	IEC/EN 61439-1 UL 508
Märkstötspänning Uimp	12 kV
Märkisolationsspänning Ui	1 000 V
Kapslingsklass IP enligt IEC 60 529	IP 2XB
Maximum operating air humidity	90 %
Driftstemperatur	-5 °C...55 °C
Förvaringstemperatur	-25 °C...75 °C
Luftfuktighet (ej kondenserande)	10...90 %
Antal anslutningar	2
Förpackningsenhet	1 st.
Nettovikt	0,65 kg
Bruttovikt	0,688 kg

Features

Tullvarukod	85369010
ETIM 9	EC001531
Produktbeskrivning	RiLineX connection adaptor for 60 mm busbar systems. To fit double connection (bar). Freely selectable phase difference. Only suitable for 10 mm busbars.

Approvals

Approvals	UL + C-UL (listed)
Explanations	Konformitetsförklaring PCF-declaration