

Rittal – The System.

Faster – better – everywhere.



SV 9614.000 Mini-PLS apparatadapter

State: 2026-05-06 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9614.000 - Mini-PLS apparatadapter

Maximal märkström på 12 A till 100 A.

Features

Art. nr.	SV 9614.000
Material	Polyamid Brandklassad enligt UL 94-V0
Färg	RAL 7035
Anslutningsledningar (AWG)	AWG 12
Märkspänning	690 V, 3~
Märkström max.	25 A
Dimension	Bredd: 54 mm Höjd: 160 mm
Profilskenor, antal/höjd	1 / 7,5 mm
Passar för tillverkare (typ)	ABB Eaton Siemens MS325 MS450 max. 25 A MS451 max. 25 A PKZM4 bis 25 A PKE65 bis 25 A 3RV10 31 bis 25 A
Förpackningsenhet	1 st.
Nettovikt	0,27 kg
Bruttovikt	0,318 kg
Kopparandel (kg/st)	0,041
Tullvarukod	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304

Features

Produktbeskrivning	SV Mini-PLS apparatadapter, 25 A, 690 V, 3-polig, anslutningskabel AWG 12, BH: 54x160 mm profilskenor H: 7,5 mm
--------------------	--

Approvals

Approvals	UR + C-UR (recognized)
-----------	------------------------

Explanations	Konformitetsförklaring Konformitetsförklaring UK
--------------	---