

# Rittal – The System.

Faster – better – everywhere.



## SV 9614.100 Mini-PLS apparatus adapter

State: 2026-05-15 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9614.100 - Mini-PLS apparatadapter

Maximal märkström på 12 A till 100 A.

## Features

Art. nr.	SV 9614.100
Material	Polyamid Brandklassad enligt UL 94-V0
Färg	RAL 7035
Anslutningsledningar (AWG)	AWG 12
Märkspänning	690 V, 3~
Märkström max.	25 A
Dimension	Bredd: 45 mm Höjd: 160 mm
Profilskenor, antal/höjd	1 / 7,5 mm
Passar för tillverkare (typ)	ABB Eaton Schneider Electric Siemens MS116 PKZM0 bis 25 A PKZM01 bis 25 A PKE12 PKE32 bis 25 A GV2-P bis 25 A GV2-RT GV2-LE10 GV3 bis 25 A 3RV10 21 3RV20 21 bis 25 A 3RV10 11 3RV20 11
Förpackningsenhet	1 st.
Nettovikt	0,25 kg

## Features

---

Bruttovikt	0,29 kg
Kopparandel (kg/st)	0,041
Tullvarukod	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304
Produktbeskrivning	SV Mini-PLS apparatadapter, 25 A, 690 V, 3-polig, anslutningskabel AWG 12, BH: 45x160 mm profilskenor H: 7,5 mm

## Approvals

---

Approvals	UR + C-UR (recognized)
Explanations	Konformitetsförklaring Konformitetsförklaring UK