

Rittal – The System.

Faster – better – everywhere.



SV 9614.100 Mini-PLS apparatus adapter

State: 2026-07-02 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9614.100 - Mini-PLS apparatadapter

Maximal märkström på 12 A till 100 A.

Features

| | |
|------------------------------|---|
| Art. nr. | SV 9614.100 |
| Material | Polyamid Brandklassad enligt UL 94-V0 |
| Färg | RAL 7035 |
| Anslutningsledningar (AWG) | AWG 12 |
| Märkspänning | 690 V, 3~ |
| Märkström max. | 25 A |
| Dimension | Bredd: 45 mm Höjd: 160 mm |
| Profilskenor, antal/höjd | 1 / 7,5 mm |
| Passar för tillverkare (typ) | ABB Eaton Schneider Electric Siemens MS116 PKZM0 bis 25 A PKZM01 bis 25 A PKE12 PKE32 bis 25 A GV2-P bis 25 A GV2-RT GV2-LE10 GV3 bis 25 A 3RV10 21 3RV20 21 bis 25 A 3RV10 11 3RV20 11 |
| Förpackningsenhet | 1 st. |
| Nettovikt | 0,25 kg |

Features

| | |
|---------------------|---|
| Bruttovikt | 0,29 kg |
| Kopparandel (kg/st) | 0,041 |
| Tullvarukod | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Produktbeskrivning | SV Mini-PLS apparatadapter, 25 A, 690 V, 3-polig, anslutningskabel AWG 12, BH: 45x160 mm profilskenor H: 7,5 mm |

Approvals

| | |
|--------------|---|
| Approvals | UR + C-UR (recognized) |
| Explanations | Konformitetsförklaring Konformitetsförklaring UK |