

Rittal – The System.

Faster – better – everywhere.



CS 9781.680

Sidogavel, fastskruvningsbar

State: 2026-05-28 (Source: [rittal.com/se-sv](https://www.rittal.com/se-sv))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CS 9781.680 - Sidogavel, fastskruvningsbar för CS Toptec, ihopbyggbart

Dubbelväggig, fastskruvningsbar sidogavel, inkl. taksidodelar.

Features

Art. nr.	CS 9781.680
Material	Aluminium AlMg3
Ytbehandling	Pulverlackerad UV-resistent ren polyester
Färg	RAL 7035
Leveransens omfattning	Sidogavlar Taksidodelar Inkl. jordnings- och fastsättningsmaterial
Passar för	Skåptyp: CS Toptec, ihopbyggbart Höjd: = 1.600 mm Djup: = 800 mm
Kapslingsklass IP enligt IEC 60 529	IP 55
Kapslingsklass NEMA	NEMA 3R NEMA 12
Grundmaterial	Aluminium
Förpackningsenhet	2 st.
Nettovikt	52,5 kg
Bruttovikt	64,5 kg
Tullvarukod	94039910
ETIM 9	EC002524
ETIM 8	EC002524
ECLASS 8.0	27182101

Features

Produktbeskrivning

CS sidogavel, dubbelväggig, för HD: 1600 x 800 mm, aluminium
AlMg3