

# Rittal – The System.

Faster – better – everywhere.



## AE 1019.500

## Compact enclosures AE

State: 18/04/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AE 1019.500 - Compact enclosures AE Stainless steel

Compact enclosure AE in stainless steel including mounting plate.

## Features

Model No.	AE 1019.500
Material	Enclosure: Stainless steel Door: Stainless steel, all-round foamed-in PU seal Mounting plate: Sheet steel Stainless steel 1.4404 (AISI 316L)
Surface finish	Enclosure and door: Brushed, grain 400, peak-to-valley height < 0.8 µm Mounting plate: Zinc-plated
Supply includes	Enclosure with door(s) Mounting plate Lock: 3 mm double-bit 3-point lock system
Protection category NEMA	NEMA 12
Protection category to IEC 60 529	IP 55
IK Code	IK08
Dimensions	Width: 1,000 mm Height: 1,200 mm Depth: 300 mm
Dimensions mounting plate (W x H)	940 mm x 1,155 mm
Number of doors	2
Lock	Lock version: 3-point lock system Number of locks: 1 Lock insert: 3 mm double-bit Material lock: Stainless steel 1.4301 (AISI 304)
Basic material	Stainless steel 1.4404 (AISI 316L)
Packs of	1 pc(s).

# Features

---

Net weight	76.4 kg
Gross weight	79.5 kg
Customs tariff number	94032080
ETIM 9	EC000261
ETIM 8	EC000261
ECLASS 8.0	27180101
Product description	AE Compact enclosure, WHD: 1000x1200x300 mm, Stainless steel 1.4404, with mounting plate, two-door, 3-point lock system

# Approvals

---

Approvals	DNV-GL UL + C-UL (listed)
Explanations	Declaration of conformity Declaration of conformity UK