


Rittal – The System.

Faster – better – everywhere.



SZ 1158.500

Metal gland plate

State: 16/05/2024 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 1158.500 - Metal gland plate

As spare/replacement part for the standard gland plates supplied loose, IP 66 when mounting in the usual position at the bottom.

Features

Model No.	SZ 1158.500
Design	Solid
Product description	As spare/replacement part for the standard gland plates supplied loose.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
Dimensions	Width: 220 mm Depth: 90 mm
To fit	Enclosure type: AE
Gland plate	Size: 2
Protection category to IEC 60 529	IP 66 when mounting in the usual position at the bottom
Packs of	6 pc(s).
Weight/pack	1.5 kg
Customs tariff number	73269098
EAN	4028177224902
ETIM 7.0	EC000211
ECLASS 8.0	27142421