

# Rittal – The System.

Faster – better – everywhere.



## SG 2371.001 Flashing light component

State: 08/07/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SG 2371.001 - Flashing light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system.

## Features

Model No.	SG 2371.001
Design	Flashing light component
Benefits	Simple assembly and contact via bayonet fastener. With 360° signal transmission thanks to optimised prism system Configuration of up to five components with the same voltage. Components are available in a range of colours and voltages.
Function principle	A modular layout is possible with connection, optical and acoustic components and a label panel
Material	Enclosure of polyamide Cap: Transparent polycarbonate
Colour	Red
Protection category to IEC 60 529	IP 65 if a cover or acoustic component is fitted at the top
Rated operating voltage	24 V (DC)
Packs of	1 pc(s).
Net weight	0.081 kg
Gross weight	0.085 kg
Customs tariff number	85311095
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220
Product description	SG LED stroboscopic light component, red

# Approvals

---

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity

---