

**Rittal – The System.**

Faster – better – everywhere.



**SZ 2561.200**

**Plastic gland plate, modular**

State: 13/06/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 2561.200 - Plastic gland plate, modular with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).



## Features

|   |   |
|---|---|
| Model No.                                 | SZ 2561.200   |
| Product description                       | Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular). |
| Material                                  | Plastic to UL 94-V0   |
| Colour                                    | RAL 7035  |
| Number of rectangular cutouts information | 1 rectangular cut-out can hold 10 small seal inserts  |
| Number of rectangular cutouts             | 2   |
| Note                                      | The allocation of gland plate sizes is indicated on the relevant enclosures   |
| No. of metric knockouts                   | 2 x M12<br>1 x M16<br>2 x M20<br>1 x M25<br>2 x M32   |

# Features

---

|                                   |   |
|-----------------------------------|---|
| Dimensions                        | Width: 256 mm<br>Depth: 149 mm  |
| To fit                            | Enclosure type: AX  |
| Gland plate                       | Size: 1   |
| Operating temperature range       | -40 °C...80 °C  |
| Protection category to IEC 60 529 | IP 66 if installed correctly  |
| Type rating to UL 50E             | Type 1<br>Type 12   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 0.24 kg   |
| Gross weight                      | 0.25 kg   |
| Customs tariff number             | 39269097  |
| ETIM 9                            | EC000211  |
| ETIM 8                            | EC000211  |
| ECLASS 8.0                        | 27142421  |
| Product description               | SZ Plastic gland plates, for AX, for cable entry, modular, pre-punched, WD: 256x149 mm, for gland plates size 1 |

# Approvals

---

|           |                  |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|