



SZ 2562.200

Plastic gland plate, modular

State: 18/04/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2562.200 - Plastic gland plate, modular with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).



Features

Model No.	SZ 2562.200
Product description	Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).
Material	Plastic to UL 94-V0
Colour	RAL 7035
Number of rectangular cutouts information	1 rectangular cut-out can hold 10 small seal inserts
Number of rectangular cutouts	3
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	3 x M12 2 x M16 3 x M20 3 x M25 2 x M32

Features

Dimensions	Width: 339 mm Depth: 149 mm
To fit	Enclosure type: AX
Gland plate	Size: 2
Operating temperature range	-40 °C...80 °C
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12
Packs of	1 pc(s).
Net weight	0.3 kg
Gross weight	0.332 kg
Customs tariff number	39269097
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Plastic gland plates, for AX, for cable entry, modular, pre-punched, WD: 339x149 mm, for gland plates size 2

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------