Rittal – The System.

Faster – better – everywhere.





SZ 2562.500 Plastic cable gland plates

State: 15/11/2025 (Source: rittal.com/sg-en)



SZ 2562.500 - Plastic cable gland plates with membranes

Simply pierce the plastic and pull through the cable, protection category IP 65 with careful cable entry.

Features

Model No.	SZ 2562.500	
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.	
Material	Plastic to UL 94-V0 Halogen free	
Colour	Similar to RAL 7035	
Note	The allocation of gland plate sizes is indicated on the relevant enclosures	
Dimensions	Width: 339 mm Depth: 149 mm	
To fit	Enclosure type: AE	
Gland plate	Size: 4	
Protection category to IEC 60 529	IP 65	
No. of cable entries and Ø (mm) minmax.	24 x 7-12 48 x 10-15 4 x 15-21 8 x 15-25 4 x 26-35	
Packs of	1 pc(s).	
Net weight	0.55	
Gross weight	0.58	
Customs tariff number	39269097	
EAN	4028177325609	
E-Number Sweden	E3404728	

© Rittal 2025

Features

ETIM 9	EC000211	
ETIM 8	EC000211	
ECLASS 8.0	27142421	

© Rittal 2025 3