### Rittal – The System.

Faster – better – everywhere.





# SZ 2563.300 Plastic gland plate

State: 30/10/2025 (Source: rittal.com/sg-en)



## SZ 2563.300 - Plastic gland plate with membranes, for AX

Simply pierce the plastic with a sharp object, and pull through the cable.

#### **Features**

Model No.	SZ 2563.300	
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.	
Material	Plastic to UL 94-V0	
Colour	Similar to RAL 7035	
Note	The allocation of gland plate sizes is indicated on the relevant enclosures	
Dimensions	Width: 447 mm Depth: 149 mm	
To fit	Enclosure type: AX	
Gland plate	Size: 3	
Protection category to IEC 60 529	IP 66 if installed correctly	
Type rating to UL 50E	Type 1 Type 12	
No. of cable entries and Ø (mm) minmax.	36 x 5-11 46 x 10-15 8 x 15-25 2 x 19-34 4 x 26-35 2 x 26-54	
Packs of	1 pc(s).	
Net weight	0.61	
Gross weight	0.63	
Customs tariff number	39269097	
EAN	4028177935754	
E-Number Sweden	E3465290	

© Rittal 2025

#### Features

ETIM 9	EC000211	
ETIM 8	EC000211	
ECLASS 8.0	27142421	

# **Approvals**

Approvals UL + C-UL - FTTA

© Rittal 2025 3