


Rittal – The System.

Faster – better – everywhere.



SZ 2563.500

Plastic cable gland plates

State: 30/01/2026 (Source: rittal.com/sg-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SZ 2563.500 - Plastic cable gland plates with membranes

Simply pierce the plastic and pull through the cable, protection category IP 65 with careful cable entry.

Features

Model No.	SZ 2563.500
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.
Material	Plastic to UL 94-V0 Halogen free
Colour	Similar to RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
Dimensions	Width: 534 mm Depth: 149 mm
To fit	Enclosure type: AE
Gland plate	Size: 5
Protection category to IEC 60 529	IP 65
No. of cable entries and Ø (mm) min.-max.	18 x 5-9 16 x 7-12 36 x 10-15 6 x 15-24 2 x 23-30 2 x 26-35 4 x 26-54 1 x 50-110
Packs of	1 pc(s).
Net weight	0.86
Gross weight	0.96
Customs tariff number	39269097
EAN	4028177325616

Features

E-Number Sweden E3404729

ETIM 9 EC000211

ETIM 8 EC000211

ECLASS 8.0 27142421