


Rittal – The System.

Faster – better – everywhere.



AX 2575.100 Metal gland plate

State: 19/04/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2575.100 - Metal gland plate with metric knockouts, for AX

Simply knock out the holes for the cable glands using a screwdriver.

Features

Model No.	AX 2575.100
Product description	Simply knock out the holes for the cable glands using a screwdriver.
Material	Sheet steel
Colour	RAL 7035
Note	The allocation of gland plate sizes is indicated on the relevant enclosures
No. of metric knockouts	2 x M12 10 x M16 8 x M20 10 x M25 2 x M32 4 x M40
Dimensions	Width: 301 mm Depth: 221 mm
To fit	Enclosure type: AX
Gland plate	Size: 5
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1 Type 12K
Packs of	1 pc(s).
Net weight	0.795 kg
Gross weight	0.806 kg
PCF per pack (cradle-to-gate)	4.1 kg CO2 eq (Cat B)

Features

Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73079100
ETIM 9	EC000211
ETIM 8	EC000211
ECLASS 8.0	27142421
Product description	SZ Metal gland plate, for AX, with metric knockouts, WD: 301x221 mm, for gland plates size 5

Approvals

Approvals	UL + C-UL - FTTA
-----------	------------------
