

Rittal – The System.

Faster – better – everywhere.



SO 2859.000 Levelling feet

State: 22/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SO 2859.000 - Levelling feet for VX, TS, VX SE in stainless steel

For mounting on enclosures, for easier floor cleaning and to compensate for floor irregularities ± 15 mm.

Features

| | |
|---|---|
| Model No. | SO 2859.000 |
| Product description | For mounting on enclosures, for easier floor cleaning and to compensate for floor irregularities ± 15 mm. |
| Benefits | Unhindered access, e.g. for floor cleaning |
| Applications | Compensation of max. 15 mm floor unevenness at the installation site |
| Material | Stainless steel 1.4301 (AISI 304) |
| Supply includes | Assembly parts |
| Max. load capacity (static) per component | 350 kg |
| To fit | Enclosure type: VX TS VX SE PC |
| Levelling range | 85 - 115 mm |
| Packs of | 4 pc(s). |
| Net weight | 3.184 kg |
| Customs tariff number | 73181900 |
| ETIM 9 | EC000721 |
| ETIM 8 | EC000721 |
| ECLASS 8.0 | 27182003 |
| Product description | SO Levelling feet, for VX, TS, VX SE, H: 85- 115 mm, stainless steel, 1.4301 |