
Rittal – The System.

Faster - better - everywhere.





SK 3174.000 Chopped-fibre filter mat

State: 04/11/2025 (Source: rittal.com/sg-en)



SK 3174.000 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

Model No.	SK 3174.000
Design	For filter holders
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 μm.
Material	Chemical fibres
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3175.000
Dimensions	Width: 338 mm Height: 242 mm Depth: 17 mm
Filter class	to DIN EN 779: G2
Packs of	3 pc(s).
Net weight	0.045
Gross weight	0.08
Customs tariff number	56039390
EAN	4028177038158
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706

© Rittal 2025

Approvals

Certificates EAC

© Rittal 2025 3