

Rittal – The System.

Faster – better – everywhere.



SK 3174.100 Chopped-fibre filter mat

State: 15/05/2026 (Source: rittal.com/sg-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3174.100 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

| | |
|--------------------------------------|--|
| Model No. | SK 3174.100 |
| Design | for roof-mounted fans |
| Product description | Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material | Chemical fibres |
| Note | Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats. |
| To fit Model No. | 3138.... 3139.... 3140.... |
| Dimensions | Width: 264 mm Height: 95 mm Depth: 17 mm |
| Filter class | to DIN EN 779: G3 |
| IP protection category to IEC 60 529 | IP 55 in roof-mounted fans |
| Packs of | 12 pc(s). |
| Net weight | 0.012 kg |
| Gross weight | 0.1 kg |
| Customs tariff number | 56039390 |
| ETIM 9 | EC002513 |
| ETIM 8 | EC002513 |

Features

ECLASS 8.0

27180706

Product description

SK spare filter mat, for roof-mounted fans, for SK 3138./3139./3140.
WHD: 264 x 95 x 17 mm

Approvals

Approvals

CSA
UR + C-UR (recognized)