Rittal - The System.

Faster – better – everywhere.





SK 3243.066 Chopped-fibre filter mat

State: 04/11/2025 (Source: rittal.com/sg-en)



SK 3243.066 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

Features

Model No.	SK 3243.066	
Design	for EMC filter fans	
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 μm.	
Material	Copper-nickel-chrome coated chemical fibres	
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.	
To fit Model No.	3243.6 3244.6 3245.6	
Dimensions	Width: 294 mm Height: 294 mm Depth: 17 mm	
Filter class	to DIN EN 779: G3	
Packs of	5 pc(s).	
Net weight	0.14	
Gross weight	0.156	
Customs tariff number	56039390	
EAN	4028177666252	
ETIM 9	EC002513	
ETIM 8	EC002513	

© Rittal 2025

Features

ECLASS 8.0	27180706

Approvals

Approvals	UR + C-UR (recognized)
Certificates	EAC

© Rittal 2025 3