

# Rittal – The System.

Faster – better – everywhere.



## SK 3301.320

## Vertical shielding

State: 28/07/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3301.320 - Vertical shielding for TS IT

To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.

## Features

Model No.	SK 3301.320
Design	Self-adhesive on one side
Product description	To block the airflow on the left and right of the 482.6 mm (19") level, for enclosure height 2000 mm.
Material	Cellular PU foam Flame-inhibiting to UL 94 (HF1)
Colour	Anthracite
Sealing between	LCP and 482.6 mm (19") level
Dimensions	Width: 210 mm Height: 1,915 mm Depth: 110 mm
To fit	Width: 800 mm
Packs of	1 pc(s).
Net weight	1.135
Gross weight	1.335
Customs tariff number	39269097
EAN	4028177504424
ETIM 9	EC002620
ETIM 8	EC002620
ECLASS 8.0	27189261

## Tender text

Thick foam rubber, 800 mm rack, vertical LCP shielding

Cellular PU foam, flame-inhibiting to UL 94 (HF1) to block the airflow on the left and right of the 482.6 mm (19 inch) level. For 800 mm wide enclosures. Length: 1900 mm, self-adhesive