

# Rittal – The System.

Faster – better – everywhere.



## SK 3321.700

# Chopped-fibre filter mat

State: 06/07/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3321.700 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

|                       |  |
|-----------------------|--|
| Model No.             | SK 3321.700  |
| Design                | for filter fans  |
| Product description   | Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm. |
| Material              | Chemical fibres  |
| Note                  | Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.  |
| To fit Model No.      | 3237.2xx/3237.1xx  |
| Dimensions            | Width: 89 mm<br>Height: 89 mm<br>Depth: 10 mm  |
| Filter class          | to DIN EN 779: G2<br>to DIN EN ISO 16890: ISO Coarse 50%   |
| Packs of              | 5 pc(s).   |
| Net weight            | 0.005 kg   |
| Gross weight          | 0.007 kg   |
| Customs tariff number | 56039390   |
| ETIM 9                | EC002513   |
| ETIM 8                | EC002513   |
| ECLASS 8.0            | 27180706   |

# Features

---

Product description

SK spare filter mats, for filter fans, for SK 3237 ..., WHD: 89 x 89 x 10 mm