


Rittal – The System.

Faster – better – everywhere.



SV 3561.000 Plate clamp

State: 17/05/2024 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3561.000 - Plate clamp

For connecting laminated copper bars, no drilling required.

Features

Model No.	SV 3561.000
Product description	For connecting laminated copper bars, no drilling required.
Material	Sheet steel
Surface finish	Zinc-plated, passivated
Clamping area for laminated copper bars (W x H)	34 x 10 mm
To fit busbars	60 x 10
To fit busbars	Busbar E-Cu
Packs of	3 pc(s).
Weight/pack	1.173 kg
Customs tariff number	85369010
EAN	4028177044371
ETIM 7.0	EC000001
ECLASS 8.0	27141146

Approvals

Explanations	Declaration of conformity Declaration of conformity UK
--------------	---

Tender text

SV plate clamps

for E-CU busbars with 3 - 10 mm thickness.

For bar width: up to 60 mm

Clamping area for laminated copper bars:

34 x 10 mm

Tightening torque

6 - 8 Nm

Material:

Sheet steel, zinc-plated, passivated