

Rittal – The System.

Faster – better – everywhere.



AS 4050.082 Busbar clammer

State: 13/03/2026 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.082 - Busbar clumper

The simple solution for clamping copper bars/busbars on Perforex BC machining centres BC and Perforex milling terminals MT.



Features

Model No.	AS 4050.082
Design	Simultaneous clamping of three short copper bars (material thickness 5 or 10 mm)
Product description	Busbar clumper for Perforex machining centres BC and Perforex milling terminals MT, for simple machining of copper bars. Suitable for drilling and thread tapping.
Machinable length with 5 mm thickness	150 - 300 mm
Machinable height (max.)	30 - 120 mm
Machinable length with 10 mm thickness	150 - 1,000 mm
Simultan_Clamping of 3 copper bars	Yes
To fit Model No.	4050.101 4055.911 4055.912
Packs of	2 pc(s).
Customs tariff number	84669360
ETIM 9	EC003010

Features

ETIM 8	EC003010
ECLASS 8.0	36609190
Product description	AS Power rail support, For easy clamping and machining of busbars., - 3 clamping positions, - L (5 mm) = 150 - 300 mm, - L (10 mm) = 150 - 1000 mm