

Rittal – The System.

Faster – better – everywhere.



AS 4050.200 Assembly frame

State: 21/08/2025 (Source: [rittal.com/sg-en](https://www.rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AS 4050.200 - Assembly frame

The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures.

Features

| | |
|---------------------------------|--|
| Model No. | AS 4050.200 |
| Design | 200 EN (electrically tilt-adjustable) |
| Product description | The assembly frames are mobile, tiltable and (depending on the version) height-adjustable frames for assembling plates and enclosures. |
| Benefits | For ergonomic, back-friendly working Individually positionable in the workshop, as it is independent from the power network Minimum space requirements during non-use Simple handling due to four castors including total lock function Variable mounting plate attachment with a quick-release fastener |
| Technical specifications | Tilt adjustment approx. 0 – 80° |
| Supply includes | Assembly frame 1 clamping unit pack, bottom 1 clamping unit pack, top Charger unit Battery |
| Note | With the assembly frame extension, a maximum machining area of 1900 x 1900 mm can be achieved. |
| Machine dimensions | Width: 1,400 mm Depth: 1,250 mm |
| Dimensions support surface max. | Width: 1,110 mm Height: 1,900 mm |
| Dimensions support surface min. | Width: 1,110 mm Height: 1,230 mm |
| Load capacity | 200 kg |

Features

| | |
|-----------------------|--|
| Working height | Working height (min.): 90 cm Working height (max.): 90 cm |
| Packs of | 1 pc(s). |
| Net weight | 130 |
| Gross weight | 148 |
| Customs tariff number | 84279000 |
| EAN | 4028177804616 |
| ETIM 9 | EC002224 |
| ETIM 8 | EC002224 |
| ECLASS 8.0 | 36659090 |

Approvals

| | |
|--------------|---------------------------|
| Explanations | Declaration of conformity |
|--------------|---------------------------|