
## Rittal – The System.

Faster - better - everywhere.





# AS 4050.770 Wire end ferrules

State: 09/12/2025 (Source: rittal.com/sg-en)



## AS 4050.770 - Wire end ferrules loose

With plastic collar.

#### **Features**

Model No.	AS 4050.770
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Yellow
Length	10 mm
AWG	18
Internal diameter	3 mm
Rittal colour code	Yes
For cross-section	1 mm²
Note	UL-certified in conjunction with the relevant tools, such as crimping machines. For bespoke advice, please contact your Rittal sales consultant.
Standards	AEH DIN 46228
To fit Model No.	4051.205 4051.210
Delivery form	Loose
Packs of	500 pc(s).
Net weight	0.5
Gross weight	0.058
Customs tariff number	85369010
EAN	4028177815735
ETIM 9	EC000005

© Rittal 2025 2

## Features

ETIM 8	EC000005
ECLASS 8.0	36659290

# **Approvals**

Approvals	UL + C-UL (listed)
	UR

© Rittal 2025 3