

# Rittal – The System.

Faster – better – everywhere.



## AS 4051.696 Wire end ferrules

State: 28/06/2026 (Source: [rittal.com/sg-en](http://rittal.com/sg-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# AS 4051.696 - Wire end ferrules on a reel

With plastic collar.

## Features

Model No.	AS 4051.696
Product description	With plastic collar.
Technical specifications	Heat-resistant to 105 °C
Material	E-Cu, galvanic tin-plated Plastic collar: Polypropylene
Colour	Grey
Length	10 mm
AWG	18
Internal diameter	2.8 mm
For cross-section	0.75 mm <sup>2</sup>
DIN colour code	Yes
Note	UL-certified in conjunction with the relevant tools, such as crimping machines.
Standards	AEH DIN 46228
Delivery form	Taped
Packs of	5,000 pc(s).
Net weight	5 kg
Customs tariff number	85369010
ETIM 9	EC000005
ETIM 8	EC000005
ECLASS 8.0	36659290
Product description	Wire end ferrules 0.75 mm <sup>2</sup> x 10 mm AWG 18, packs of 5,000 pc(s)., colour: grey, delivery form: on belt (in accordance with the DIN colour code)

# Approvals

---

Approvals

UL + C-UL (listed)